



Equipment Rack, 4-Post, 29 in (737 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | 4 post rack |

General Specifications

| | |
|---------------------------|-----------|
| Color | Black |
| Rack Type | EIA 19 in |
| Rack Units | 52 |
| Rail Mounting Hole | #12-24 |

Dimensions

| | |
|------------------------------|---------------------|
| Height | 2,438.4 mm 96 in |
| Channel Width | 76.2 mm 3 in |
| Width | 518.16 mm 20.4 in |
| Depth | 1,041.4 mm 41 in |
| Dimensional Standards | EIA-310-E |

Material Specifications

| | |
|----------------------|-------------------------|
| Finish | Powder-coated, textured |
| Material Type | Aluminum |

Mechanical Specifications

| | |
|---------------------------|-------------------------|
| Static Load Rating | 907.2 kg 2,000.031 lb |
|---------------------------|-------------------------|

Packaging and Weights

| | |
|-----------------|--|
| Included | Base pan Forty #12-24 x 1/2 in mounting screws Four vertical rack rails Instruction sheet Twenty four 3/8 in split lock washers Twenty four 3/8-16 UNC x 1 in hex head |
|-----------------|--|

760082537 | RK4P52-29A

bolts | Twenty four 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

| | |
|---------------------------|----------------------|
| Packaging quantity | 1 |
| Packaging Type | Flat packed |
| Weight, net | 41.28 kg 91.007 lb |

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

