

# CHD-2U-W



SYSTIMAX® CHD 2U sliding tray fiber panel, accepts (24) CHD ULL modules, splice cassettes or MPO panels, providing up to 144 duplex LC ports or up to 144 MPO ports, white, High Speed Migration

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	CHD

## General Specifications

<b>Application</b>	Accepts 24 CHD Universal Modules, or CHD MPO/LC adapter packs
<b>Color</b>	White
<b>Interface, front</b>	Unloaded
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	538.48 mm   21.2 in

## Packaging and Weights

<b>Weight, net</b>	8.8 kg   19.4 lb
--------------------	------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

# CHD-2U-W

---

UK-ROHS

Compliant

