MX6-SPL6030-1440-U



OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit up, Putty white, 2.2 mts

Alternative products available:

MX6-SPL6030-A-U7Z4 OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit up, Putty white, 7 ft

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Fiber entrance cabinet
Product Brand	OMX600®
Product Series	OMX
General Specifications	
Access	Front
Cable Entry Location	Тор
Cable Exit Location	Тор
Color	Putty white
Mounting	Concrete floor
Splice Trays Included, quantity	0
Splicing Capacity Note	up to 5184 ribbon fibers
Splicing Capacity, maximum	5184
Dimensions	
Height	2200 mm 86.614 in
Width	600 mm 23.622 in
Depth	300 mm 11.811 in

Environmental Specifications

Environmental Space

Indoor

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



MX6-SPL6030-1440-U

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

