

# SSC-760241465N4 | 12 in Pole Top for Nokia or Samsung



Top of Pole 12in Dia Concealment Enclosure for up to two Airscale Micro radios and/or LAA/CBRS radios or one Samsung LAA or CBRS

- Enclosure for holding 2 Nokia Airscale Micro LAA/CBRS radios
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

-Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

-Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

-Supports (1) "RT4401-48A" or (1) "RT2201-46A" Samsung radio with included adapter bracket. Power Supply to be located in mid pole enclosure.

-Supports AWHQN with separately available kit "860664329-AMK-001"

-Supports DK antenna with separately ordered "MTM106001" bracket.

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Pole top
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, CommScope</b>	CommScope Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   DK   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Concrete poles   Metal poles   Non-tapered poles   Tapered poles   Wood poles

# SSC-760241465N4 | 12 in Pole Top for Nokia or Samsung

---

**Radio Compatibility, Nokia** (2) Airscale micro radios (Including LAA & CBRS models) | AHIA | AHIB | AZRB

**Radio Compatibility Samsung** RT2201-46A | RT4401-48A

**Radios Included** None

## Dimensions

**Height** 762 mm | 30 in

**Width** 304.8 mm | 12 in

**Depth** 304.8 mm | 12 in

**Mounting Bolt Circle Diameter** 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Aluminum | Steel

## Environmental Specifications

**Thermal Compliance** GR-487

## Packaging and Weights

**Volume** 0.056 m<sup>3</sup> | 1.97 ft<sup>3</sup>

**Weight (unloaded)** 18.144 kg | 40 lb

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines