FBVLCUC11

Base Product



LazrSPEED® 550 WideBand LC/UPC to Unconnectorized, Fiber Pigtail, 0.9 mm SBJ

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber pigtail, unjacketed

Product Brand SYSTIMAX InstaPATCH® 360

Product Series FBV

Ordering Note Minimum length may vary based on cable configuration

General Specifications

Color, boot A Lime green

Color, connector A Black
Interface, Connector A LC/UPC

Jacket Color Lime green

Total Fibers, quantity 1


Dimensions

Cable Assembly Length Range (m) 1 - 20
Cable Assembly Length Range (ft) 1 - 66

Ordering Tree



FBVLCUC11



Mechanical Specifications

Cable Retention Strength, maximum $2.00 \text{ lb} @ 90 \degree | 5.00 \text{ lb} @ 0 \degree$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity 2

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted

UK-ROHS Compliant



Included Products

860657285 - LC/PC Connector, Multimode, Lime

COMMSCOPE®

FBVLCUC11

