

# 1-1989801-0

---



RJ45 Patch Cord, category 6, black, 10 ft

## Product Classification

<b>Regional Availability</b>	Latin America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type</b>	Stranded
<b>Interface, Connector A</b>	RJ45 plug
<b>Interface, Connector B</b>	RJ45 plug
<b>Jacket Color</b>	Black
<b>Pairs, quantity</b>	4

## Dimensions

<b>Cord Length</b>	3.05 m   10.007 ft
<b>Compatible Conductor Gauge, stranded</b>	24 AWG

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

1-1989801-0

---

