

F1-NMNM-1M-NC

FSJ1-50A Jumper with interface types N Male and N Male, 1 m



Product Classification

Product Type	SureFlex® standard
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	1 m 3.281 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss (dB)
6000–7000 MHz	1.44	15	0.92
7000–8000 MHz	1.44	15	1.1

Jumper Assembly Sample Label

F1-NMNM-1M-NC



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

- F1PNM-HF – Type N Male for 1/4 in FSJ1-50A cable