



ION® Active Intelligent Point of Interface Subrack with Guide Rails

OBSOLETE

Product Classification

Product Type	Point of interface subrack
Product Brand	ION®

General Specifications

General Alarm	Integrated into management system
Interface Slots Available, quantity	1
Mounting	Rack
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Rack Type	EIA 19 in
Slots Available, quantity	8

Dimensions

Height	177 mm 6.969 in
Width	483 mm 19.016 in
Depth	422 mm 16.614 in

Electrical Specifications

Electrical Safety Standard	EN 60950
Power Consumption	276 W
Voltage Range	+10 to +14 Vdc

Environmental Specifications

Operating Temperature	+5 °C to +55 °C (+41 °F to +131 °F)
Storage Temperature	-25 °C to +70 °C (-13 °F to +158 °F)
Relative Humidity	46%–94%
Mean Time Between Failures (MTBF) at Temperature	213,000 h @ 25 °C

Packaging and Weights

Height, packed	530 mm 20.866 in
Width, packed	295 mm 11.614 in
Depth, packed	600 mm 23.622 in
Included	Guide rails
Weight, gross	8 kg 17.637 lb
Weight, net	7 kg 15.432 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system