## DB224-A

1-port omni exposed dipole antenna, 150–160 MHz, 360° HPBW, fixed electrical tilt

- Broad response
- Two-piece mast for ease of shipping

## General Specifications

Antenna Type Omni

**Band** Single band

**Color** Silver

**Grounding Type** RF connector inner conductor and body grounded to reflector and mounting bracket

Performance Note Outdoor usage

Radiator MaterialAluminumRF Connector InterfaceN MaleRF Connector LocationBottom

RF Connector Quantity, low band 1
RF Connector Quantity, total 1

**Dimensions** 

**Length** 6477 mm | 255 in

Net Weight, without mounting kit  $15.9 \text{ kg} \mid 35.053 \text{ lb}$ 

Electrical Specifications

**Impedance** 50 ohm

**Operating Frequency Band** 150 – 160 MHz

**Polarization** Vertical

### **Electrical Specifications**

Frequency Band, MHz 150-160

Gain, dBi 8.1

Beamwidth, Horizontal,

360

degrees

Beamwidth, Vertical, degrees 16

COMMSC PE®

## DB224-A

Beam Tilt, degrees

VSWR | Return loss, dB 1.5 | 14.0 Input Power per Port, 500

maximum, watts

#### Mechanical Specifications

**Wind Loading @ Velocity, maximum** 560.5 N @ 100 mph (126.0 lbf @ 100 mph)

Wind Speed, maximum 130 km/h (81 mph)

0

## Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

DB365-OS – Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 -

3.5 in (35 - 89 mm) OD round members.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance



# DB365-0S

Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.

#### **Product Classification**

**Product Type** Pipe mounting kit

General Specifications

ApplicationOutdoorColorSilver

**Dimensions** 

Compatible Diameter, maximum88.9 mm | 3.5 inCompatible Diameter, minimum33 mm | 1.299 inWeight, net3.2 kg | 7.055 lb

Material Specifications

Material Type Galvanized steel

#### Packaging and Weights

Included Brackets | Hardware

Packaging quantity 2

**Weight, gross** 3.6 kg | 7.937 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



