

# 760199968 | M81C-Coupler

---

## M81C Coaxial Coupler, Pro white



### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Multimedia coupler

### General Specifications

<b>Application</b>	Module designed for video applications
<b>Color</b>	Pro white
<b>Mounting</b>	Snap-in

### Dimensions

<b>Height</b>	17.526 mm   0.69 in
<b>Width</b>	18.542 mm   0.73 in
<b>Depth</b>	12.7 mm   0.5 in

### Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

### Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0

### Packaging and Weights

**Packaging quantity** 25

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

