SEC

Base Product



NOVUX™ SEC Splice/Patch Closure

The NOVUX SEC closure design is optimized for building façade applications. The SEC closure connects as many as eight customers and is agnostic to connectivity technologies (splice, connector, field-installable connector) for agility and flexibility. The innovative removable hinge design allows cover to open from the left, right, or top. Optional hinge locking mechanism is available for extra security. Identification plate for either QR code or customer logo are available.

The SEC closure is offered in two types:

SEC3:

Color is black (RAL 9005)

SEC4:

Color is gray (RAL 7035)

Key features of the NOVUX closures:

- NOVUX is the industry's most flexible FTTX platform. It takes modularity to new levels with technologies that span the end-to-fiber network from the trunk to the drop. That makes it the go-to FTTX platform for virtually every application today and in the future.
- NOVUX was designed from the ground up to help service providers gain access to the supplies they need —when and where they need them. And with the power of CommScope's global supply chain, service providers can trust that they'll be able to tackle even the largest FTTX deployments.
- With NOVUX, ordering, configuration, and training are all easier on the service provider's staff. With common components and installation procedures, it helps overcome craft labor shortages and reduce field errors, too.

Product Classification

Regional Availability EMEA

Regional Availability Note Contact your local CommScope representative for specific availability

Product Type In-line, rectangular fiber closure

Product Brand NOVUX™

Product Series SEC

General Specifications

Cable Capacity, Branch 2 Round 8.0–12.0 mm (0.31–0.47 in)

Cable Capacity, Drop 6 Round 3.0-6.0 mm (0.12-0.23 in) for pre-connectorized cables | 6 Round 3.0-7.0 mm (0.12-

0.27 in)

Page 1 of 4

SEC

Cable Capacity, Feeder 2 Round 8.0–12.0 mm (0.31–0.47 in)

Cable Ports Quantity, total10 round ports

Cable Sealing Type Gasket/grommet configuration

Closure Sealing Type Hinged with lock

Closure Style In-line

Color Black | Gray

Mounting Facade | Wall

Network Area Type Drop

Splicing Type, Supported Single fusion


Dimensions


 Height
 130 mm | 5.118 in


 Width
 216 mm | 8.504 in

 Depth
 87 mm | 3.425 in

Dimension Drawing







Port Configuration




SFC



(*Upgrade kit includes one cover and two additional trays, and increases splice capacity from 12 to 36 splices.)

Ordering Tree



Optical Specifications

Fiber Type G.657.A1 | G.657.A2 | G.657.B3

Environmental Specifications

Page 3 of 4

SEC

Environmental Space Facade | Outdoor

Qualification Standards IP55

UV Resistance UV stabilized

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

