AEKT-E1



Antenna Enclosure Kit

- Innovative flexible modular solution enabling suitable sites to be upgraded to 5G capability
- The module installs directly above an existing, suitable passive antenna to provide the appearance of a single integrated antenna unit – potentially simplifying site zoning approvals
- Installed antenna units can be swapped out on site e.g. to perform capacity upgrades
- Compatible specifically with antennas featuring CommScope's 498 x 197 mm (WxD) radome housing
- Can be deployed as a standalone solution
- Compatible with certain specific Ericsson Active Antenna System Products (AAS)
- Includes Antenna Enclosure Housing, Installation Kit for compatible Ericsson mMIMO Active Antenna (AAS), AEKT-E1 Mounting Hardware, protective "Windshield" Panels and Top Cap
- A Mounting Kit for the antenna installed below the AEKT-E1 unit should be ordered separately, Commscope P/N: BSAMNT-AEKT (required when installing the AEKT-E1 module directly on top of an antenna)
- Contact your CommScope representative for further details

General Specifications

Antenna Type Antenna enclosure kit

Color Light Gray (RAL 7035)

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

Dimensions

Width 498 mm | 19.606 in

Depth 199 mm | 7.835 in


Length 1100 mm | 43.307 in


Net Weight, without mounting kit 9.29 kg | 20.481 lb

Application Drawing



AEKT-E1





Mechanical Specifications

Effective Projective Area (EPA), frontal

Effective Projective Area (EPA), lateral

Wind Loading @ Velocity, frontal

Wind Loading @ Velocity, lateral

Wind Loading @ Velocity, rear

Wind Speed, maximum

0.66 m² | 7.104 ft²

 $0.29 \ m^2 \ | \ 3.122 \ ft^2$

700.0 N @ 150 km/h (157.4 lbf @ 150 km/h)

308.0 N @ 150 km/h (69.2 lbf @ 150 km/h)

700.0 N @ 150 km/h (157.4 lbf @ 150 km/h)

241 km/h (150 mph)

Packaging and Weights

Width, packed 620 mm | 24.409 in

Depth, packed 350 mm | 13.78 in

COMMSCOPE®

AEKT-E1

 Length, packed
 1430 mm | 56.299 in

 Included
 Brackets | Hardware

 Weight, gross
 25.94 kg | 57.188 lb

 Weight, net
 19.65 kg | 43.321 lb

Regulatory Compliance/Certifications

Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

AEKTMNT-E1 – Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round

members

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



AEKTMNT-E1



Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Product Classification

Product Type Pipe mounting kit

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant

