



| ZONE | REV. | ECR | DESCRIPTION | DRAWN BY | DATE |
|------|------|------------|---------------|----------|-----------|
| - | A | 8000004900 | INITIAL ISSUE | H.H | 2014/8/21 |



RVVPX303.6F12R2

| | | | |
|---|--|--|---|
| | | | |
| <small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETRES. TOLERANCES ARE:</small> 0 - 20 ±2 HOLE Ø ±1.0 >20-100 ±2 HOLE Ø ±1.0 >100-200 ±2 ANGULAR ±1.0° >200 ±2 | | DESCRIPTION: PRODUCT DRAWING PART/DWG NUMBER: RVVPX303.6F12R2 | |
| DRAWN TO AS1100 | | 3D MOD: N/A DRAWN: H.H | DWG REV: A DATE: 2014/8/21 SCALE: 1:5 A3 SHEET 1 OF 1 |