

1 2 3 4 5 6 7 8 9 10 11 12

A

B

C

D

E

F

G

H

100

A

B

C

D



E

F

G

H

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 8000034101: REL TO PRODUCTION PER EAO 606535.	31OCT19 NH	SG/YK



RV4S4-65A-R6

DENSITY	g/mm ³
MASS	Kg
VOLUME	mm ³
SURFACE AREA	mm ²
HEIGHT	
LENGTH	
WIDTH	

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE X ±	2 PLACE .XX ±		
1 PLACE .X ±	ANGLES ±		
FINISH		MATERIAL	
N/A			
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 & 2, THIRD EDITION (2002)</small>		NAME	DATE
		CE NH1031	31OCT19
		RW NH1031	11/13/2019
		RV SG1108	11/14/2019
		AD KY1009	11/14/2019
RE AC1095	11/14/2019	TITLE	
ECN 8000034101-O		PRODUCT DRAWING	
SIZE	WORK AREA	SCALE	DOCUMENT NO.
A2	23	1:6	RV4S4-65A-R6-L
		MODEL	DRAWING
VERSION	STATUS	REVISION	VERSION
01	RE	B	00
		STATUS	REVISION
		RE	A
			SHEET
			1 OF 1

1 2 3 4 5 6 7 8 9 10 11 12