

HGS620 Icon Strip (Voice / Data / Blank), Black (25 ea/pkg)



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Icon kit
<b>Ordering Note</b>	Minimum order quantity, 20 packs

## General Specifications

**Color** Black

## Dimensions

**Height** 13.97 mm | 0.55 in

**Width** 23.62 mm | 0.93 in

**Depth** 2.79 mm | 0.11 in

## Material Specifications

**Material Type** High-impact, flame retardant, thermoplastic

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging quantity** 25

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

