760243389 | SFC-LCAF-09-8Y-12-PACK



Qwik-Fuse Connector, LC, Singlemode-APC, Green, for 250µm/900µm, 12 per pack

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

Product Brand Qwik | TeraSPEED®

Product Series Qwik-Fuse

General Specifications

Body Style BTW
Color, boot Green
Color, housing Green

Ferrule Geometry Factory polished

Interface LC/APC

Interface Feature Field Installable | Fusion splice

Dimensions

Tube Length 32 mm | 1.26 in

Compatible Cable Diameter 0.25 mm | 0.01 in | 0.9 mm | 0.035 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 0.74 lb @ 0 ° | 1.03 lb @ 0 °

Optical Specifications



760243389 | SFC-LCAF-09-8Y-12-PACK

Fiber Mode Singlemode

Fiber Type OS2

Optical Components Standard ANSI/TIA-568. 3-D | GR-326-CORE | IEC 61753-1

Insertion Loss, maximum0.3 dBInsertion Loss, typical0.15 dBReturn Loss, minimum65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity 12

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

