



Cushion Insert with 1 hole for 1/2 in corrugated coaxial cable

## Product Classification

<b>Product Type</b>	Cushion insert
<b>Product Brand</b>	I-Line
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cable Type</b>	Corrugated
<b>Cables per Cushion</b>	1
<b>Color</b>	Black

## Dimensions

<b>Height</b>	82.55 mm   3.25 in
<b>Length</b>	25.4 mm   1 in
<b>Nominal Size</b>	1/2 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Environmental Specifications

<b>UV Resistance Test Method</b>	MIL-STD-810E, Procedure 11, Method 505
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66

## Packaging and Weights

<b>Height, packed</b>	170.18 mm   6.7 in
-----------------------	--------------------

# 294684

---

<b>Width, packed</b>	129.54 mm   5.1 in
<b>Length, packed</b>	99.06 mm   3.9 in
<b>Included</b>	Cushion
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.8 kg   1.764 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

