

Cold shrink Kit for 5/8 in to 1/4 in through 1/2 in connections



Product Classification

Product Type	Cold shrink kit
Ordering Note	CommScope® non-standard product

General Specifications

Application	Provides additional moisture seal for cable connections
Applications per Kit	One 1/4 in–1/2 in to 5/8 in
Cable Family	ETS1-50T FSJ1-50B FSJ1-75 FSJ4-50B FSJ4-75A LDF1-50 LDF4-50A LDF4-75 LDF4.5-50
Color	Black

Dimensions

Width	53.848 mm 2.12 in
Length	254 mm 10 in
Cable Diameter for Seal, maximum	20.32 mm 0.8 in
Cable Diameter for Seal, minimum	7.37 mm 0.29 in
Inner Diameter	51.31 mm 2.02 in
Nominal Size	1/2 in 1/4 in 5/8 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

UV Resistance Test Method	UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation	≥1000 hours

241475-13

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

Height, packed 292.1 mm | 11.5 in
Width, packed 78.74 mm | 3.1 in
Length, packed 78.74 mm | 3.1 in
Included One EPDM rubber tube | One sealing foam strip
Packaging quantity 1
Weight, gross 0.16 kg | 0.353 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

