

# 33938-5

---

Single Entrance Panel for 5 in coaxial cable

## Product Classification

<b>Product Type</b>	Entrance panel
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Color</b>	Gray
<b>Entry Panel Port Size</b>	162.56 mm   6.4 in
<b>Number of Ports</b>	1
<b>Panel Type</b>	Single

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	76.2 mm   3 in
<b>Nominal Size</b>	5 in

## Material Specifications

<b>Material Type</b>	Aluminum
----------------------	----------

## Environmental Specifications

<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

## Packaging and Weights

<b>Height, packed</b>	304.8 mm   12 in
<b>Width, packed</b>	76.2 mm   3 in
<b>Length, packed</b>	304.8 mm   12 in
<b>Included</b>	Boot   Clamp   Plate
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	2.92 kg   6.437 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

# 33938-5

---

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

