

# 760053199 | KIT-CLEANING/INSPECT



## Cleaning and Inspection Kit, Fiber Optic

### Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio** CommScope®

**Product Type** Fiber cleaning and inspection kit

### General Specifications

**Compatible Interface** LC | MPO | SC

### Packaging and Weights

**Included** Carrying case | Fiber cleaning solution, 3 oz | Forty cleaning swabs, 1.25 mm | Forty cleaning swabs, 2.5 mm | HD4i Digital Display | Instruction sheet | LC Bulkhead Probe Tip | LC Duplex FMAE Series Probe Adapter | LC I.B.C. | LC and SC Simplex Couplers | MPO coupler, aligned-keys | MTP/MPO Bulkhead Probe Tip | MTP/MPO I.B.C | One slot reel cleaner | P5000i inspection probe with universal 2.5mm tip and barrel assembly for FBP and FiberChek Probes | SC Bulkhead Probe Tip | SC I.B.C. | Universal 1.25mm Patch Cord Tip | Universal Flare Adapter for FMAE Probe Adapters | VFL with 1.25 mm and 2.5 mm Adapter Caps

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



### Included Products

# 760053199 | KIT-CLEANING/INSPECT

---

- 1918803-1 – One slot reel cleaner for 1.25 mm and 2.5 mm ferrule connectors, MPO/MTP without pins (female), and MT-RJ without pins (female)
- 1918809-1 – Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)
- 2064499-1 – Fiber Optic SC IBC (In Bulkhead Cleaner)
- 2064500-1 – Fiber Optic LC IBC (In Bulkhead Cleaner)
- 760249056 – Fiber Optic Visual Fault Locator with 2.5 and 1.25 mm Adapter Caps, for connectors such as  
VFL with 2.5mm & 1.25 mm Caps SC, ST, FC, LC and MU



One slot reel cleaner for 1.25 mm and 2.5 mm ferrule connectors, MPO /MTP without pins (female), and MT-RJ without pins (female)

- Handles more than 400 cleanings per cleaner

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cleaning kit

## General Specifications

<b>Color</b>	Blue
<b>Compatible Connector Type</b>	FC   LC   MPO (female)   MT-RJ (female)   SC   ST

## Dimensions

<b>Height</b>	83 mm   3.268 in
<b>Width</b>	48 mm   1.89 in
<b>Length</b>	127 mm   5 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)



- Cleans male or female MTP/MPO connectors
- Handles more than 400 cleanings per cleaner

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cleaning kit

## General Specifications

<b>Color</b>	Blue
--------------	------

## Dimensions

<b>Height</b>	56.5 mm   2.224 in
<b>Width</b>	22 mm   0.866 in
<b>Length</b>	184.2 mm   7.252 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Fiber Optic SC IBC (In Bulkhead Cleaner)



- Simple pushing motion to engage tool
- Audible CLICK to alert the operator when tools is fully engaged
- Dry cleaning strand eliminates the need for solvents to be effective
- Over 525+ engagements per unit

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cleaning kit

## General Specifications

<b>Color</b>	Blue
<b>Interface</b>	SC

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted





Fiber Optic LC IBC (In Bulkhead Cleaner)

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   Latin America   North America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber cleaning kit

## General Specifications

<b>Color</b>	Blue
<b>Interface</b>	LC

## Dimensions

<b>Height</b>	17.5 mm   0.689 in
<b>Width</b>	17.5 mm   0.689 in
<b>Length</b>	181 mm   7.126 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant





# 760249056 | VFL with 2.5mm & 1.25 mm Caps



Fiber Optic Visual Fault Locator with 2.5 and 1.25 mm Adapter Caps, for connectors such as SC, ST, FC, LC and MU

- Locate sharp bends, breaks, and damages in fiber
- Conduct end-to-end continuity tests
- Perform fiber tracing and identification
- Compact, ergonomic design for ultimate portability
- Visible wavelength is 650 nm
- High powered laser (1 mW) for single-mode (> 7 km) and multi-mode (> 5 km) connectors
- Continuous or Flash illumination
- 2.5 mm and 1.25 mm connector inputs

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Tool kit

## General Specifications

<b>Compatible Connector Type</b>	FC   LC   SC   ST
----------------------------------	-------------------

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Included</b>	2 AAA Batteries   Pouch   VFL with 1.25 mm and 2.5 mm Adapter Caps
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

