

# BC-30-10D

---



Pipe-to-Pipe Clamp, joins two 1-1/2 in to 3-1/2 in OD round members

## Product Classification

**Product Type** Clamp set

## General Specifications

**Mounting** Pipe-to-pipe

**Tower Taper** Non-tapered | Tapered

## Dimensions

**Height** 5 in | 127 mm

**Width** 8 in | 203.2 mm

**Length** 10 in | 254 mm

**Mounting Diameter 2, maximum** 3.5 in | 88.9 mm

**Mounting Diameter 2, minimum** 1.5 in | 38.1 mm

**Mounting Diameter, maximum** 3.5 in | 88.9 mm

**Mounting Diameter, minimum** 1.5 in | 38.1 mm

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamp halves | Threaded rod

**Packaging quantity** 2

**Weight, net** 12.2 kg | 26.896 lb