

CC-215



Crossover Clamp, joins 1-1/2 in to 2-1/2 in OD pipe to 2-3/8 in to 5 in OD pipe

Product Classification

Product Type Clamp set

General Specifications

Mounting Crossover clamp

Taper Non-tapered

Dimensions

Height 127 mm | 5 in

Width 203.2 mm | 8 in

Length 127 mm | 5 in

Mounting Diameter 2, maximum 127 mm | 5 in

Mounting Diameter 2, minimum 60.96 mm | 2.4 in

Mounting Diameter, maximum 63.5 mm | 2.5 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 1

Weight, net 4.1 kg | 9.039 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system