

# CTBC-2

---



Crimping Tool for CNT-195 and CNT-240 connectors

## Product Classification

<b>Product Type</b>	Tool
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Application</b>	Crimps the ferrule for CNT® connectors
<b>Tool Type</b>	Crimp tool

## Dimensions

<b>Crimp Die Diameter</b>	5.08 mm   0.2 in   7.62 mm   0.3 in
<b>Wrench Opening</b>	0 mm   0 in

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Torque Value</b>	0 in lb   0 N-m
---------------------	-----------------

## Packaging and Weights

<b>Height, packed</b>	20.32 mm   0.8 in
<b>Width, packed</b>	99.06 mm   3.9 in
<b>Length, packed</b>	279.4 mm   11 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.66 kg   1.455 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

# CTBC-2

---

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

