

MCPT-3812



EASIAx® Manual Cable Preparation Tool for FSJ2-50 and FSJ4-50B coaxial cable

Product Classification

Product Type	Tool
Product Brand	EASIAx Plus®
Ordering Note	CommScope® non-standard product

General Specifications

Application	Prepares cable for connector attachment
Cutting Blade Life	25 cable preparations
Cutting Blades Included	1
Jacket Blades Included	1
Tool Type	Manual cable preparation tool

Dimensions

Nominal Size	1/2 in 3/8 in
Wrench Opening	0 mm 0 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Torque Value	0 in lb 0 N-m
---------------------	-----------------

Packaging and Weights

Height, packed	93.98 mm 3.7 in
Width, packed	76.2 mm 3 in
Length, packed	50.8 mm 2 in
Packaging quantity	1
Weight, gross	0.27 kg 0.595 lb

MCPT-3812

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

