

SSH-M



SnapStak® Plus Adjustable Hanger for 14mm to 25mm Cable - No Grommets Required. For patents, see www.cs-pat.com.

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak® Plus
Ordering Note	CommScope® non-standard product

General Specifications

Accessories	Hangers
Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder
Patent Number	US 9,866,004

Dimensions

Maximum Stack Height	2
Maximum Stack Height, Coaxial	2
Height	67.1 mm 2.642 in
Width	38.1 mm 1.5 in
Length	48.5 mm 1.909 in
Compatible Cable Diameter Range	14–25 mm
Compatible Diameter, maximum	25 mm 0.984 in
Compatible Diameter, minimum	14 mm 0.551 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

SSH-M

Material Type Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥1000 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Flammability Test Method UL 2043

Packaging and Weights

Height, packed 33 cm | 12.992 in

Width, packed 6.4 cm | 2.52 in

Length, packed 26 cm | 10.236 in

Packaging quantity 10

Weight, gross 0.53 kg | 1.168 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power