

ST-BSP60



Ballast Pole, 60 ft

- Bolt-together ballast tray foundation
- No digging required
- Removable step pegs
- Collar mounting

Product Classification

Product Type Monopole

General Specifications

Application Multi-point telecommunications | Point-to-point communications

Equipment Load Rating 18 in microwave reflector | Omni antenna | Telecommunications unit

Foundation Non-penetrating above ground design with aggregate fill

Monopole Capability Type Medium duty

Monopole Design Round conical

Optional Accessories Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts

Dimensions

Height 18.288 m | 60 ft

Mounting Diameter, maximum 304.8 mm | 12 in

Mounting Diameter, minimum 101.6 mm | 4 in

Base Area 8 ft x 8 ft

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Ballast tray | Ground tab | Hand holes | Lightning rod | Monopole | Safety climb systems | Safety-climb | Step pegs

Packaging quantity 1

ST-BSP60

Weight, net

517.5 kg | 1,140.891 lb