UGBKIT-0214-T



x 355.6 mm)

Product Classification

Product Type	Grounding bar
Ordering Note	CommScope® non-standard product
Dimensions	
Height	50.8 mm 2 in
Length	355.6 mm 14 in
Material Thickness	6.35 mm 0.25 in
Hole Size	7/16 in 7/16 in x 5/8 in
Hole Distance, center to center	19.05 mm 0.75 in
Material Specifications	
Material Type	Tinned copper
Packaging and Weights	
Height, packed	403.86 mm 15.9 in
Width, packed	121.92 mm 4.8 in
	121.92111111 4.0111
Length, packed	63.5 mm 2.5 in
Length, packed Included	
	63.5 mm 2.5 in Galvanized angle adapter Grounding bar Insulators Mounting

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023



UGBKIT-0214-T

ROHS

UK-ROHS

Compliant Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

COMMSCOPE®