# 760245190 | FST-T2-0610-A0250F



FST-T2 Flexible Service Terminal, 12f, 6 Port x 2 Fiber, 6 HMFOC Adapters (Jack/male/pinned), 2 fibers per adapter at drop side, Stub at feeder side, black, 250 ft/76 m

- Flexible Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Flexible structure allowing installation in constrained spaces

#### **Product Classification**

Regional Availability North America

**Product Type** Access terminal, with multi-fiber port

**Product Series** FST-T2

Minimum Order Quantity

#### General Specifications

Cable Type Dielectric - Loose Tube

Cable, quantity 7

**Distribution Type** 6 ports

**Drop Port Type**Hardened multi-fiber (HMFOC) adapter

**Drop Port, quantity** 6

Enclosure Color Black

Mounting Handhole | Pedestal

Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Port, quantity 6

Splitter, quantity 0

**Stub Type** Stub tail

#### **Dimensions**

**Height** 112.5 mm | 4.429 in

**Width** 53 mm | 2.087 in

**Depth** 31 mm | 1.22 in

Cable Length, stub 250 ft (76 m)


**COMMSCOPE®** 

## 760245190 | FST-T2-0610-A0250F

#### **Cable Outer Diameter**

4.1 x 7.6 mm (0.16 x 0.30 in)

### Ordering Tree



#### Material Specifications

**Enclosure Material Type**Engineered plastic

**Optical Specifications** 

**Fiber Type** G.657.A1/A2

Operating Wavelength Range 1310 – 1550 nm

Attenuation Single Ports, maximum 0.65 dB

Return Loss, Connector, minimum 65 dB

## **Environmental Specifications**

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** 5%-100%, condensing

Environmental Space Above ground | Below ground | Buried

Qualification Standards IEC 61300, 1 m waterhead | Telcordia GR-3120-CORE | Telcordia GR-3152-CORE

**UV Resistance** UV stabilized

Packaging and Weights

**COMMSCOPE®** 

# 760245190 | FST-T2-0610-A0250F

**Included** Mounting hardware

Packaging quantity 1

Packaging Type Box | Carton

Weight, without cable 0.23 kg | 0.507 lb

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

