DFJ-12S320B



Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Wireless Fiber Cable Assemblies

Product Brand HELIAX®
Product Series DFJ

Ordering Note CommScope® non-standard product

General Specifications

Construction Type Discrete fiber tail | Discrete fiber trunk

 Interface, Connector A
 HMFOC

 Interface Body Style, connector A
 Straight

Interface, Connector B Unterminated

Interface Feature, connector BOutdoorInterface Body Style, connector BStraightJacket ColorBlackTotal Fibers, quantity12

Dimensions


Cable Assembly Length Range (ft) 300 - 500

Diameter Over Jacket 6 mm | 0.236 in

Ordering Tree



DFJ-12S320B



Optical Specifications

Fiber Type G.657.A2/B2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.75

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Environmental Space Outdoor

Packaging and Weights

Cable weight 37.1 kg/km | 24.93 lb/kft

COMMSCOPE®

DFJ-12S320B

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

