

PREMIUM Certificate

no. c6049d-20

Customer:

CommScope INC.
1100 CommScope Place SE
28603 Hickory, North Carolina, USA

VALID TO MAY 2022

Category 7A

Test sample(s):

Balanced cable:

CommScope Netconnect Cat. 7A S/FTP Solid PR04 AWG22 LSFRZH

CommScope Netconnect Cat. 7A S/FTP Solid PR04x2 AWG22 LSFRZH

Part-no.: CS67Z3 C7A 4/22 S/FTP – Dca;
CS67ZC C7A 4/22 S/FTP – Cca;
CS67ZB C7A 4/22 S/FTP – B2ca;
CS67Z3 C7A 8/22 S/FTP – Dca;
CS67ZC C7A 8/22 S/FTP – Cca;
CS67ZB C7A 8/22 S/FTP – B2ca

Applied standard(s):

ISO/IEC 11801-1 Ed.1.0 (2017-11)
IEC 61156-5 Ed.3.0 (2020-04)

Result(s):

The sample meets the limits of the applied standards and regulations with respect to the parameters indicated above.

Balanced cable, copper, Category 7A

GHMT PREMIUM Verification Program, GHMT PVP

Ongoing compliance with the specifications is monitored within the framework of regular sampling, which cannot be influenced by the customer, thus defining high standards as regards continuous manufacturing quality.

This Certificate refers to the comprehensive test report no. R6049d-20 and shall only be applicable in conjunction with the test report.

Bexbach, 30. November 2021



Dirk Wilhelm, engineer
(Chairman of the Managing Board)



*Test laboratory accredited by DAkkS in accordance with DIN EN ISO/IEC 17025:2018.
The accreditation is valid for the test methods listed in certificate D-PL-17559-01-00.*

GHMT AG

In der Kolling 320
66450 Bexbach / Germany

PO box 11 16
66442 Bexbach / Germany

T: +49 6826 92 28-0
F: +49 6826 92 28-290

info@ghmt.de
www.ghmt.de

**RELIABILITY IN TOTAL
REQUIRES ACCURACY IN DETAIL.**