

243684-M



Angle Adapter, compact, M10 tapped hole

Product Classification

Product Type	Adapter
Ordering Note	CommScope® non-standard product

General Specifications

Adapter Type	Angle adapter
Mounting	M10 tapped hole

Dimensions

Inside Width	0.63 in 16.002 mm
Outside Width	1.5 in 38.1 mm
Inside Length	0.63 in 16.002 mm
Outside Length	1.85 in 46.99 mm
Material Thickness	0.117 in 2.972 mm

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Installation Torque, maximum	13 ft lb 17.626 N-m
Installation Torque, minimum	11 ft lb 14.914 N-m
Maximum Loading	Double stack, 1-5/8 in cable

Packaging and Weights

Height, packed	14 cm 5.512 in
-----------------------	------------------

243684-M

Width, packed	14 cm 5.512 in
Length, packed	11 cm 4.331 in
Packaging quantity	10
Weight, gross	1.59 kg 3.505 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system