

250057-45B



Round Base, 45 mm stand-off, for RCT RADIAX® Coupling Mode Radiating cable

Product Classification

Product Type	Base
Product Brand	RADIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Adapter Type	Stand-off adapter
Color	Black

Dimensions

Height	44.958 mm 1.77 in
Width	44.958 mm 1.77 in
Length	0.046 m 0.15 ft

Material Specifications

Material Type	Polyamide PA6
----------------------	---------------

Environmental Specifications

Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Flammability Test Method	UL 94 V-0
Toxicity Index Test Method	IEC 60754-2
UV Resistance, minimum with no degradation	≥500 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	19.5 cm 7.677 in
Width, packed	13.5 cm 5.315 in
Length, packed	30.5 cm 12.008 in
Packaging quantity	100

250057-45B

Weight, gross

2.46 kg | 5.423 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

