


760253535 | M2400A-1U-GS-WH



M2400 1U Angled Modular Panel, 24 port (MGS600 / MGS400 / UNJ10GT), White

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Brand	GigaSPEED X10D®
Product Series	M Series

General Specifications

ANSI/TIA Category	6 6A
Cable Type	Unshielded
Color	White
Intelligence Type	Passive
Panel Style	Angled
Rack Type	EIA 19 in
Rack Units	1
Total Ports, quantity	24

Dimensions

Height	43.69 mm 1.72 in
Width	482.6 mm 19 in
Depth	138.18 mm 5.44 in
Compatible Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Compatible Diameter Over Dielectric, minimum	0.762 mm 0.03 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

760253535 | M2400A-1U-GS-WH

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

