

# RF-NL10-B

---

Non-Penetrating Roof Frame, 10 ft face, pipe not included



## Product Classification

**Product Type** Non-penetrating roof frame

## General Specifications

**Mounting** Non-penetrating  
**Note** Four 96 in x 18 in panel antennas per sector  
**Pipe, quantity** 0

## Dimensions

**Height** 1905 mm | 75 in  
**Face Width** 3.2 m | 10.5 ft  
**Width** 3,200.4 mm | 126 in  
**Length** 2.53 m | 8.3 ft  
**Pipe Length** 0 mm | 0 in  
**Pipe Outer Diameter** 88.9 mm | 3.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479  
**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Rubber mats, with or without pipe mounts

# RF-NL10-B

---

**Packaging quantity** 1  
**Weight, net** 227 kg | 500.449 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## \* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code