

# TF-GM4-96

---



## Guy Tower Face Mount, 4 ft face

### Product Classification

**Product Type** Tower face mount

### General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

**Pipe, quantity** 1

**Tower Taper** Non-tapered

### Dimensions

**Height** 2,438.4 mm | 96 in

**Face Width** 1.219 m | 4 ft

**Width** 1,219.2 mm | 48 in

**Length** 304.8 mm | 12 in

**Pipe Length** 2,438.4 mm | 96 in

**Face Support Pipe Diameter** 60.96 mm | 2.4 in

**Mounting Diameter, maximum** 203.2 mm | 8 in

**Mounting Diameter, minimum** 0 mm | 0 in

**Pipe Outer Diameter** 114.3 mm | 4.5 in

### Material Specifications

**Material Type** Hot dip galvanized steel

### Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL

**Wind Rating Test Method** TIA/EIA-222

### Packaging and Weights

# TF-GM4-96

---

<b>Included</b>	Crossover plates   Pipes   Saddle mounts
<b>Packaging quantity</b>	1
<b>Weight, net</b>	114.986 kg   253.5 lb

## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--