

F-CLAMP-B2-2B



KwikClamp™ Hanger for power & fiber cables, two 7-22 mm holes (alongside each other), double block; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8-25 mm

Dimensions

Maximum Stack Height	2
Height	167 mm 6.575 in
Width	56 mm 2.205 in
Length	46 mm 1.811 in
Compatible Cable Diameter Range	7-22 mm
Compatible Diameter, maximum	22 mm 0.866 in
Compatible Diameter, minimum	7 mm 0.276 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic Stainless steel
----------------------	--------------------------------------

F-CLAMP-B2-2B

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Five times cable weight

UV Resistance, minimum with no degradation

≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs

Packaging and Weights

Height, packed

15.5 cm | 6.102 in

Width, packed

30.5 cm | 12.008 in

Length, packed

35.5 cm | 13.976 in

Included

Hardware

Packaging quantity

24

Weight, gross

5.136 kg | 11.323 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power