F-CLAMP-C-1B



KwikClamp™ Hanger for power & fiber cables, 22-34 mm, single stack; includes hardware

Product Classification

Product TypeHanger kitProduct BrandKwikClamp™

Ordering Note CommScope® standard product in Europe, the Middle East, and

Africa

General Specifications

Cables per Hanger 1

Color Black

Hanger Type KwikClamp[™] hanger

Mounting 3–25 mm angle iron | 3–25 mm flat plate | Round Member 8-

 $25\,mm$

Dimensions

Maximum Stack Height

 Height
 140 mm | 5.512 in

 Width
 45 mm | 1.772 in

 Length
 44 mm | 1.732 in

Compatible Cable Diameter Range 22–34 mm

Compatible Diameter, maximum34 mm1 .339 inCompatible Diameter, minimum22 mm0 .866 inHanger Spacing, maximum1.83 m6 .004 ft

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Page 1 of 2



F-CLAMP-C-1B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Corrosion Resistance, minimum with no degredation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 15.5 cm | 6.102 in

 Width, packed
 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 42

Weight, gross 5.514 kg | 12.156 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power