


# BUDI-R24JC0309A | BUDI-R24JC0309A



BUDI™ Rapid Terminal, 24-position, SC/APC, Indoor/Outdoor riser cable, MPO at far end, 100 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   Europe   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Rapid distribution terminal
<b>Product Brand</b>	BUDI™   RapidReel®
<b>Product Series</b>	BUDI-R
<b>Warranty</b>	For more information, please consult our Product Warranty guidelines

## General Specifications

<b>Functionality</b>	Patching   Slack storage
<b>Adapters, quantity</b>	24
<b>Cable Entry Location</b>	Bottom
<b>Cable Sealing Type</b>	Gasket/grommet configuration
<b>Cable Type</b>	Indoor/outdoor - Stranded
<b>Color</b>	Gray
<b>Distribution Type</b>	24 ports
<b>Interface</b>	SC/APC
<b>Interface, stub</b>	MPO
<b>Lock Type</b>	Security screw
<b>Mounting</b>	Wall mount
<b>Port, quantity</b>	24

## Dimensions

<b>Height</b>	270 mm   10.63 in
<b>Width</b>	214 mm   8.425 in

# BUDI-R24JC0309A | BUDI-R24JC0309A

---

<b>Depth</b>	125 mm   4.921 in
<b>Cable Length</b>	30 m   98.425 ft
<b>Enclosure Size</b>	Small

## Material Specifications

<b>Material Type</b>	Polycarbonate ABS (PC-ABS)
----------------------	----------------------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Environmental Space</b>	Indoor/Outdoor
<b>Flammability Rating</b>	UL 94 V-0
<b>Qualification Standards</b>	IEC 61753-1   UL

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Carton

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--