FL2-S2702A008-DD00



FL2000 Fiber Termination Panel, 24 SC/UPC, singlemode, 2RU, 23 in, putty white, pre-terminated with IFC cable, 8 meters, Stub tail at far end

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with IFC cable

Product Series FL2000

General Specifications

Functionality Patching

Adapter Packs Included, quantity 4

Cable Exit Location Downward

Cable Stub Type IFC

Color Putty white

Growth Configuration Fully loaded

Interface, front SC/UPC

Interface, rear Stub tail

Rack Type EIA 23 in

Rack Units 2

Shelf Movement Hinged

Splicing Capacity, maximum 0

Total Ports, quantity 24

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 584.2 mm | 23 in


Depth 256.54 mm | 10.1 in

Cable Length 8 m | 26.247 ft



FL2-S2702A008-DD00

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights



FL2-S2702A008-DD00

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

