

# SSC-760237600 | Radio Enclosure Micro for Sam, Nokia, Erc Radios



Middle of Pole Micro Concealment Enclosure for up Low, Mid, and High Power Samsung, Ericsson, and Nokia Radios

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760237600E1x Ericsson  
SSC-760237600S1x Samsung  
SSC-760237600N1x Nokia  
SSC-760237600N3x Nokia

Includes Standard Mounting kit for through bolt, clamp, and banding

Available After Market KIts, ordered separate:  
-860649584S-xx 5" Standoff for wood poles  
-860649584ST-xx Standoff for Round Tapered Poles

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Mid pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Non-tapered poles   Tapered poles   Wood poles
<b>Power Supply Compatibility</b>	CCI PSU-1200W-48-N   DELTA 1.0   DELTA 2.0   PSU-AC-08
<b>Radio Compatibility, Ericsson</b>	220x   440x   4415   4426   4435   4449   4455   8843   Diplexer   PSU-AC-08   Power Distribution
<b>Radio Compatibility, Nokia</b>	AHBCA   AHFIA   AHFIB   AHFIC   AHLBA   CCI   Diplexer   Power Distribution

# SSC-760237600 | Radio Enclosure Micro for Sam, Nokia, Erc Radios

---

**Radio Compatibility Samsung** Diplexer | Power Distribution | RF4402D-D1A | RFV01U-D1A | RT2201-46A | RT4401-48A

**Radios Included** None

## Dimensions

**Height** 1,117.6 mm | 44 in

**Width** 533.4 mm | 21 in

**Depth** 508 mm | 20 in

## Electrical Specifications

**Power/Fiber Input** Trade size knockouts at rear side

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Aluminum | Steel

## Environmental Specifications

**Thermal Compliance** GR-487

## Packaging and Weights

**Volume** 0.303 m<sup>3</sup> | 10.7 ft<sup>3</sup>

**Weight (loaded)** 136.078 kg | 300 lb

**Weight (unloaded)** 49.895 kg | 110 lb

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines