



OCAB Outdoor fiber distribution cabinet - innerwork

Cabinet innerwork for up to 144f customer connections

- 96 up to 144 Point-to-multipoint positions, SC & LC footprint
- 8 branch-off blown fibre Ø5,7& 8mm microtube positions
- 4 branch-off blown fibre Ø 12mm microtube positions
- 144 direct drops blown fibre Ø5,7 & 8mm microtube positions
- Up to 12 OCM1 LGX Style Fiber Optic Splitter Module positions
- Transient-free, modular, flexible fibre management
- FIST single-circuit and single-element splice trays
- Up to 768 splices (including SC trays 256 splices)
- Storage area for looped cable
- Compatible with all fibre types: G.652D and G.657 series
- Fast and simple installation

Product Classification

Regional Availability	EMEA
Product Type	Fiber cross-connect hub
Product Series	OCAB

General Specifications

Color	Light Gray (RAL 7035)
Mounting	Cabinet

Dimensions

Height	960 mm 37.795 in
Width	640 mm 25.197 in
Depth	222 mm 8.74 in

Material Specifications

Finish	Powder coated polyester
---------------	-------------------------

Packaging and Weights

Packaging quantity	5
---------------------------	---

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

