# CW1527-000 | FDC-W8-FAT-S1/8-10NN-1N-INT



FDC Fiber Optic Splice/Patch Closure, Gel Cable Sealing, 8 SC/UPC Adapters, 24 fusion splices

#### **Product Classification**

Regional Availability Asia

**Product Type** Single-ended, rectangular fiber closure

Product Series FDC

General Specifications

Cable Ports Quantity, total4 round ports + 8 round ports

Cable Sealing TypeCompressed gelClosure Sealing TypeHinged with latch

Closure Style Single-ended

**Color** Black

Mounting Manhole | Pedestal | Strand | Wall

Port Type SC/UPC

Port, quantity 8

Splice Tray Included, quantity 1

**Splice Tray Type Included** 24-way, heat shrink

**Splitter Type** No splitter

Splitter, quantity 0

**Dimensions** 

 Height
 237 mm | 9.331 in

 Width
 76.5 mm | 3.012 in

 Length
 266 mm | 10.472 in

Material Specifications

Material Type Rugged polymer



# CW1527-000 | FDC-W8-FAT-S1/8-10NN-1N-INT

### **Environmental Specifications**

Environmental Space Above ground | Below ground

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

#### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

