


760074278 | VP360-19PNL-KT



GigaSPEED X10D® VisiPatch® 360 19 In. 1U Panel with required connection hardware

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Panel assembly
Product Brand	VisiPatch®

General Specifications

Product Design	VisiPatch® 360
ANSI/TIA Category	6A

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	Austel CE UL cUL

Packaging and Weights

Included	Four #12-24 x 0.50 in screws Instruction sheet Label sheet Panel Sixteen connecting blocks Two index strips Two label holders Two wiring block covers Two wiring blocks
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

