1920523-2 | OCP-S2-O2MASEN-XX



Fiber Optic Pigtail, Simplex, Singlemode, SC/APC to Stub, 0.9 mm diameter, 2 m

Product Classification

Regional Availability	EMEA
Product Type	Fiber pigtail, jacketed
Product Series	OCP

General Specifications

Connector A, quantity	1
Color, boot A	Green
Color, connector A	Green
Interface, Connector A	SC/APC
Jacket Color	Yellow
Total Fibers, quantity	1
Dimensions	

Cord Length 2 m | 6.562 ft

Ordering Tree

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024



1920523-2 | OCP-S2-02MASEN-XX

OCP - XX - XX M XXX - XX Connector/adapter type Standard C Superior B Type grade grade SC/UPC S1 SF SC/UPC S2 SG SC/APC 8° S3 SH SC/APC 9° L1 LF LC/UPC L2 LG LC/APC - EC LSH/APC 8°

Fiber

type

A1

A2

- Standard Configuration by default 900µm buffer buffer color : yellow 250 µm color : natural or milky white

Optical Specifications

Singlemode

Fiber Type G.657.A1, TeraSPEED®

Environmental Specifications

Environmental Space

Fiber Mode

Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

50

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024

