

760150540 | SFC-SC/APC-16-GR

Field Installable Connector, SC, Singlemode-APC, Green, for 1.6 mm

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Connector kit
Product Brand	TeraSPEED®
Product Series	Qwik-Fuse

General Specifications

Body Style	Simplex
Color	Green
Ferrule Geometry	Pre-radiused
Interface	SC/APC

Dimensions

Length	56 mm 2.205 in
Compatible Cable Diameter	1.6 mm 0.063 in

Material Specifications

Ferrule Material	Zirconia
-------------------------	----------

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °
--	----------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D and G.657.A1 OS2
Optical Components Standard	ANSI/TIA-568. 3-D
Insertion Loss, ULL, typical	0.3 dB
Return Loss, minimum	65 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

