


# 6-557965-3 | MP-64U-FS-1



Modular Plug, 6P/4C, unshielded, small conductor, flat oval, 0.74 – 0.86 mm insulation OD, category 3, 100/bag

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Modular plug

## General Specifications

<b>ANSI/TIA Category</b>	3
<b>Cable Type</b>	Flat oval, unshielded
<b>Conductor Type</b>	Solid   Stranded
<b>Interface</b>	RJ11
<b>Positions/Loaded Contacts</b>	6/4
<b>Termination Type</b>	IDC

## Dimensions

<b>Compatible Cable Diameter, maximum</b>	6.61 mm   0.26 in
<b>Compatible Cable Diameter, minimum</b>	2.29 mm   0.09 in
<b>Compatible Insulated Conductor Diameter, maximum</b>	0.86 mm   0.034 in
<b>Compatible Insulated Conductor Diameter, minimum</b>	0.74 mm   0.029 in
<b>Contact Plating Thickness</b>	1.27 µm
<b>Compatible Conductor Gauge, solid</b>	28–26 AWG
<b>Compatible Conductor Gauge, stranded</b>	28–26 AWG

## Electrical Specifications

<b>Current Rating, maximum</b>	0.75 A
<b>Insulation Resistance, minimum</b>	500 mOhm

# 6-557965-3 | MP-64U-FS-1

---

**Safety Voltage Rating** 150 Vac

## Material Specifications

**Contact Base Material** Phosphor Bronze

**Contact Plating Material** Gold

**Material Type** Glass filled polycarbonate

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

**Safety Standard** UL 1863

## Packaging and Weights

**Packaging quantity** 100

**Packaging Type** Bag | Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

