

## SnapSeal™ Entry Cushion with 6 holes for 1/4 in corrugated coaxial cable



### Product Classification

<b>Product Type</b>	Entry cushion
<b>Ordering Note</b>	CommScope® non-standard product

### General Specifications

<b>Cable Type</b>	Corrugated
<b>Cables per Cushion</b>	6
<b>Color</b>	Black

### Dimensions

<b>Height</b>	101.6 mm   4 in
<b>Length</b>	31.75 mm   1.25 in
<b>Nominal Size</b>	1/4 in

### Material Specifications

<b>Material Type</b>	Thermoplastic elastomer (TPE)
----------------------	-------------------------------

### Environmental Specifications

<b>UV Resistance Test Method</b>	MIL-STD-810E, Procedure 11, Method 505
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.9.0

### Packaging and Weights

<b>Height, packed</b>	170.18 mm   6.7 in
<b>Width, packed</b>	129.54 mm   5.1 in

# SEC-614

---

<b>Length, packed</b>	99.06 mm   3.9 in
<b>Included</b>	Compression ring   SnapSeal™ entry cushion
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.8 kg   1.764 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

