760252620 | FDC-W8-FAT-AE3-NN-0-NN-72



FDC Fiber access terminal for aerial applications, 3 mm / 3x2 mm drop cable rubber sealing, no Adapters, 72 fusion splices

Product Classification

Regional Availability EMEA | Latin America | Middle East/Africa | North America

Product Type Single-ended, rectangular fiber closure

Product Series FDC

General Specifications

Cable Ports Quantity, total4 round ports + 8 round ports

Cable Sealing TypeCompressed rubber

Closure Sealing Type Hinged with latch | Hinged with latch, bolts and rubber H seal

Closure Style Single-ended

Color Black

Mounting Facade | Strand | Wall

Port Type No adapter

Port, quantity

Splice Tray Included, quantity 3

Splicing Capacity, Mass Fusion, maximum 72

Splitter Type No splitter

Splitter, quantity 0

Dimensions

 Height
 76.5 mm | 3.012 in

 Width
 237 mm | 9.331 in

 Length
 285 mm | 11.22 in

Cable Entry Drop Port Diameter3 mm (0.12 in) mm | 3x2 mm (0.12x0.08 in) mm

Cable Entry Main Port Diameter6 mm (0.24 in) mmMain Cable Diameter, maximum14 mm | 0.551 in

Material Specifications

COMMSCOPE®

760252620 | FDC-W8-FAT-AE3-NN-0-NN-72

Material Type Rugged polymer

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

