760252622 | FDC-W8-FAT-AE5-S1-8-18-24



FDC Fiber access terminal for aerial applications, 5 mm drop cable rubber sealing, 8 SC/UPC Adapters, 1:8 pre-inst SC/UPC splitter, 24 fusion splices

Product Classification

Regional Availability EMEA | Latin America | Middle East/Africa | North America

Product Type Single-ended, rectangular fiber closure

Product Series FDC

General Specifications

Cable Ports Quantity, total4 round ports + 8 round ports

Cable Sealing TypeCompressed rubber

Closure Sealing Type Hinged with latch | Hinged with latch, bolts and rubber H seal

Closure Style Single-ended

Color Black

Mounting Facade | Strand | Wall

Port Type SC/UPC

Port, quantity 8

Splice Tray Included, quantity 1

Splice Tray Type Included 24-way, heat shrink

Splitter Type 1 x 8

Splitter, quantity 1

Dimensions

 Height
 76.5 mm | 3.012 in

 Width
 237 mm | 9.331 in

 Length
 285 mm | 11.22 in

 Cable Entry Drop Port Diameter
 5 mm (0.20 in) mm

 Cable Entry Main Port Diameter
 6 mm (0.24 in) mm

 Main Cable Diameter, maximum
 14 mm | 0.551 in

Material Specifications

COMMSC PE°

760252622 | FDC-W8-FAT-AE5-S1-8-18-24

Material Type

Rugged polymer

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

