

# SYSTIMAX® HD Fiber Panel Announcement: New Product *Global Communication*

CommScope® announces the addition of six new fiber panels to the SYSTIMAX® High Density (HD) fiber solution family. The solution combines high density with manageability and ease of making moves, additions and changes. At the heart of the SYSTIMAX® HD solution is the 1U, 2U and 4U HD fiber panels. In addition to the HD sliding panels which are shipping today, the HD fixed panels and HD splicing panels are available to order starting immediately. Each of the fiber panels accepts InstaPATCH® 360Modules, MPO connector pass-through panels, or 360G2 pigtail cassettes. and can be upgraded to add AIM (Automated Infrastructure Management) based intelligence.



## Ordering Information:

Please visit eCatalog for product specs <http://www.commscope.com/Product-Catalog/Enterprise/>

## SYSTIMAX® HD Sliding Panels

Part Number	Product Code	Descriptions
760209940	HD-1U	SYSTIMAX® HD 1U sliding fiber panel, accepts (4) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 48 duplex LC ports or up to 32 MPO ports
760209957	HD-2U	SYSTIMAX® HD 2U sliding fiber panel, accepts (8) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 96 duplex LC ports or up to 64 MPO ports
760209965	HD-4U	SYSTIMAX® HD 4U sliding fiber panel, accepts (16) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 192 duplex LC ports or up to 128 MPO ports

## SYSTIMAX® HD Fixed Panels

Part Number	Product Code	Descriptions
760210732	HD-1U-FX	SYSTIMAX® HD 1U fixed fiber panel, accepts (4) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 48 duplex LC ports or up to 32 MPO ports

Part Number	Product Code	Descriptions
760210740	HD-2U-FX	SYSTIMAX® HD 2U fixed fiber panel, accepts (8) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 96 duplex LC ports or up to 64 MPO ports
760210757	HD-4U-FX	SYSTIMAX® HD 4U fixed fiber panel, accepts (16) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 192 duplex LC ports or up to 128 MPO ports

### SYSTIMAX® HD Splicing Panels

Part Number	Product Code	Descriptions
760231506	HD-1U-SP	SYSTIMAX® HD 1U Splicing fiber panel, accepts (4) 360G2 pigtail cassettes or 360DP panels, providing field term/splice capability up to 48 duplex LC ports
760231514	HD-2U-SP	SYSTIMAX® HD 1U Splicing fiber panel, accepts (8) 360G2 pigtail cassettes or 360DP panels, providing field term/splice capability up to 96 duplex LC ports
760231522	HD-4U-SP	SYSTIMAX® HD 1U Splicing fiber panel, accepts (16) 360G2 pigtail cassettes or 360DP panels, providing field term/splice capability up to 192 duplex LC ports

### SYSTIMAX® HD Panels with imVision AIM

Part Number	Product Code	Descriptions
760217414	HD-iP-1U-96F-LC-DM-LS-SD	HD iPATCH 1U 96F-LC Distribution Module, LazrSPEED, Sliding Shelf
760217422	HD-iP-1U-96F-LC-DM-TS-SD	HD iPATCH 1U 96F-LC Distribution Module, TeraSPEED, Sliding Shelf
760217448	HD-iP-2U-192F-LC-DM-LS-SD	HD iPATCH 2U 192F-LC Distribution Module, LazrSPEED, Sliding Shelf
760217455	HD-iP-2U-192F-LC-DM-TS-SD	HD iPATCH 2U 192F-LC Distribution Module, TeraSPEED, Sliding Shelf
760217463	HD-iP-1U-32-MPO-DP-SD	HD iPATCH 1U 32-MPO Distribution Panel, Sliding Shelf
760217471	HD-iP-2U-64-MPO-DP-SD	HD iPATCH 2U 64-MPO Distribution Panel, Sliding Shelf